

Assembly workbench series V, with lowerable transport unit

With 3 drawers, 100% full extension, wheeled



Execution:

- Worktop made of solid beechwood, thickness 50 mm, sandable, glued in bars
- Robust, welded sheet steel construction
- Base made of square-section steel tube 45 x 45 x 2 mm, stationary, load capacity 1500 kg with evenly distributed load
- Vice, 100 mm jaw width with hinged lifter, can be rotated by 360° and height-adjustable
- Vice compartment fitted with one door which can be closed again after the vice has been folded out
- With lowerable transport unit, the drive/stop position is adjusted by simply turning the lever on the front side of the workbench

Advantage:

- Worktop with special tothing, therefore extremely robust and virtually unlimited service life
- Always mobile and ready for use anywhere thanks to transport unit



Art. no.	50284 843
Working height	850 mm
Number of steering rollers	4 PCS
Worktop width	1270 mm
Number of drawers	3 PCS
Worktop height	50 mm
Worktop depth	700 mm
Pullout type	Full extension
On castors	Yes
Moving device, can be lowered	Yes
Colour of front	Optional
Cabinet colour	Optional
Model	704V
With single pull-out safety brake	Yes
Surface	Powder-coated
With wheel lock	No
Load-carrying capacity	1500 kg
Levelling	Yes
Dynamic load-carrying capacity	450 kg
Wheel diameter	100 mm
Type	mobile/retractable
Lock type	DOM® locking system
Material of worktop	Solid beech
Folding vice	Yes
Drawer front height	1 x 90 mm, 1 x 180 mm, 1 x 270 mm
Material	Sheet steel
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of wheel	Polyurethane
Product Group	Prod. Gr. 502

EAN

4014641018665