

2002-12-13

ELFA

PRODUKTINFORMATION


Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

ELFA artikelnr
54-462-24 Stegmotor 17HD1008

HYBRID STEPPING MOTOR TYPE 17HD1008

General specifications		Electrical specifications		Wiring Diagram
Step Angle	1.8°±5%	Rated voltage	8 V	
Number of phase	4	Rated current	0.8A	
Insulation resistance	100Mohm Min.(500V DC)	Resistance per phase	10±10% ohm	
Insulation class	Class B	Inductance per phase	17±20% mH	
Rotor inertia	38 g·cm ²	Holding torque	4.1 kg·cm	
Weight	0.24 kg	Detent torque	150 g·cm	

Dimensions unit=mm



受控图纸
 日期 **2002年6月4日**
 上海鸣志电器有限公司

comment:	A					STANDARD	<i>[Signature]</i> 02.6.4
						APPROVE	<i>[Signature]</i> 02.6.4
	REV.	NO.	MAK.	QTY.	CR.NO.	DESIGN	<i>[Signature]</i> 02.6.3