



## M8 MALE FLANGE PLUG FRONT MOUNT

TPE wires 3x0.25 0.2m



Front mounting  
Flange M8 male  
with multi-strand wire  
3-pole

### [Link to Product](#)

#### Illustration



Male



Product may differ from Image

**Form**

08552

**Technical Data**

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

**Cables**

Cable number	970
No./diameter of wires	3 × 0.25 mm <sup>2</sup>
Wire isolation	PP (br, bk, bl)
Shore hardness outer jacket	70 ± 5D
Outer diameter	approx. 1.25 mm
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

**General data**

Temperature range	-25...+85 °C
-------------------	--------------

**Commercial data**

country of origin	DE
customs tariff number	85444290
minimum order quantity	1