

Clip, 10.3 x 38 mm, UR



20 A (UL)

**Description**

- Through hole mounting

Standards

- UL 4248-1 / UL 512

Approvals

- UL File Number: E41738

Applications

- Combiner Boxes in Photovoltaic Systems



References**Weblinks**

pdf, General Product Information, Approvals, RoHS, CHINA-RoHS, e-Store, SCHURTER-Stock-Check, Distributor-Stock-Check

Technical Data

Fuse-Link	10.3 x 38 mm
Mounting	PCB
Terminal	Solder THT
Rated Current	20A (UL)
Degree of Protection	IP 00
Material: Terminals	see variants
Unit Weight (Socket/Cap)	4.1 g
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	☐, Type, Approvals

Soldering Methods	Wave
Solderability	235 °C / 2 sec acc. to IEC 60068-2-20, Test Ta, method 1
Resistance to Soldering Heat	260 °C / 10 sec acc. to IEC 60068-2-20, Test Tb, method 1A

Abmessungen


Drilling diagram

Variants

Clip	Terminal	Material: Terminals	Order Number
●	Straight	Tin-Plated Bronze	7170.0470

Packaging Unit Bulk (50 pcs.)