

## LT-LED LT-LED MV and LT-LED 110/230V



CE – certified to EMC directive 2004/108/EC.  
Complies with low voltage directive 2006/95/EC.  
High voltage transient and polarity reversal protected.  
Operating temperature: -20°C to + 55°C.



<b>Mains 110/230V</b>	amber > 6cd red > 10cd	65 flashes/min 6 bursts/flash	85–265 Vac	IP67	148gms
<b>Multivoltage MV</b>			10–100Vdc		

### Features:

A compact LED beacon with low power consumption.

- Multivoltage 10–100Vdc, and mains 110Vac and 230Vac versions
- Flashing and continuously lit modes
- Clear lens with coloured LEDs
- Low power consumption
- 3 year guarantee
- Weatherproof to IP67

### Materials:

Polycarbonate lens and base. ROHS compliant.

### Accessories:

**FX2**  
mounting  
base



**FX40**  
mounting  
bracket



**FX39**  
mounting  
pole



Product	<i>i</i> flashing	<i>i</i> constant	Amber	Red
<b>Mains 110/230V</b>	15mA @ 110Vac 10mA @ 230Vac		448002	448003
<b>Multivoltage MV</b>	110mA @ 12Vdc 55mA @ 24Vdc 35mA @ 50Vac 25mA @ 100Vac	80mA @ 12Vdc 40mA @ 24Vdc 25mA @ 50Vac 20mA @ 100Vac	446002	446003

  

76 mm

95 mm

3 x 5.5mm holes

22.5 mm

45 mm