

NADB15FF

15 pole D-SUB feedthrough, female to female, D-shape nickel housing

Features & Benefits

- Ideal for audio networking and integration of equipment into video systems
- Universally accepted standard D-shape housing



Technical Information

Product

Title	NADB15FF
Gender	female - female

Electrical

Contact resistance	30 mΩ
Insulation resistance	> 5 GΩ
Number of electrical contacts	15
Rated current per contact	3 A
Rated voltage	50 V ac
Dielectric strength	> 0.5 kVac

Mechanical

Panel thickness	4 mm
Wiring	Feedthrough
Mounting direction	Front mounting
Chassis shape	D

Material

Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Insert	Steel , tin plated, PBT
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel

Environmental

Flammability	UL 94 V-0
Temperature range	-25 °C to +85 °C

Accessories

SCCD-W



SCDP-*



SCDX



NZP1RU-12



NZP1RU-8

