


Coaxial Cable Connector 16_MCX-50-2-14/133_N

Description

Right angle cable plug

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0012 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006021
Catalogue drawing	DOU-00006016
Assembly instruction	DOC-0000179229

Ordering Information

Single package	16_MCX-50-2-14/133_NE
Bulk 100 pcs package	16_MCX-50-2-14/133_NH

Additional Information

Suitable cables	ENVIROFLEX_316, RG_316_/U, RG_188_A/U, RG_174_/U
-----------------	--