

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200905080](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Receptacle, M8 x 1.0 Mounting Threads, Male (Straight) with Back Mounting Pins, with 5 Poles on Mating Side

Documents:

3D Model	Drawing (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Industrial Receptacles
Series	120090
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Type	Bulkhead Feed-Through
UPC	883906784577

Physical

Coupling Type	External Thread
Gender	Male
Keyway	None
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 1.0
Net Weight	4.120/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical


Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Material Info

Engineering Number	4R5F46000
--------------------	-----------

Reference - Drawing Numbers

Sales Drawing	SD-120090-005
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ECHA_01_2020 (16 January 2020)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120090 Series](#)