

Adjustable clamps

Depressed centre



Version:

- Heat-treated steel
- Painted
- Single depressed centre



Art. no.	26138 100
Slot width	26 mm
Length	250 mm
Suitable cheese-head screw DIN 912	M24
Slot length	80 mm
Clamping shoe height	35 mm
Clamping shoe width	70 mm
Height	32 mm
Width 3	35 mm
Height 2	25 mm
DIN	6316

EAN-Code

4020772071110