

Standard 98N handheld measuring probes

Accessories for UCI hardness tester SonoDur

NewSonic

Application:

Hand-held sensor 98 N (10 kgf) for mobile UCI hardness tester SonoDur. Ideal for EN ISO 1090, structural steel, cast iron and forged parts, mounting elements.



Execution:

- Stainless steel housing

Delivery:

Hand-held sensor without connecting cable, including handle and manufacturer's certificate

Art. no.	42170 715
Brand	NEWSONIC
Manufacturer Part Number	2215667
Test force	98 N
Test body diameter	25 mm
Manual probe length	176 mm
Gross Weight	0.275 kg
Product Group	486