

Assembly workbench series V - stationary

With 3 drawers, 100% full extension



Execution:

- Worktop made of solid beechwood, thickness 50 mm, sandable, glued in bars
- Robust, welded sheet steel construction
- Base made of square-section steel tube 45 x 45 x 2 mm, stationary, load capacity 1500 kg with evenly distributed load
- Vice, 100 mm jaw width with hinged lifter, can be rotated by 360° and height-adjustable
- Vice compartment fitted with one door which can be closed again after the vice has been folded out

Advantage:

- Worktop with special tothing, therefore extremely robust and virtually unlimited service life



Art. no.	50284 860
Number of drawers	3 PCS
Working height	850 mm
Number of doors	1 PCS
Worktop width	1270 mm
Pullout type	Full extension
Worktop height	50 mm
Colour of front	Anthracite grey RAL 7016
Worktop depth	700 mm
Cabinet colour	Light grey RAL 7035
With single pull-out safety brake	Yes
Levelling	Yes
Lock type	DOM® locking system
Drawer front height	1 x 90 mm, 1 x 180 mm, 1 x 270 mm
Model	804V
Drawer width (inner dimension)	500 mm
Surface	Powder-coated
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	1500 kg
Drawer depth (inner dimension)	540 mm
Dynamic load-carrying capacity	450 kg
Load-carrying capacity per drawer	100 kg
Material of worktop	Solid beech
Central locking	Yes
Material	Sheet steel
Product Group	Prod. Gr. 502

EAN

4014641157807