

Pneumatic chipping hammer RRH-4309K

Reduced vibration



Advantage

- For left-handed and right-handed users

Art. no.	75066 111
Brand	RED ROOSTER
Manufacturer Part Number	RRH-4309K
Model	RRH-4309K
Impact energy	9 J
Max. impact rate	3200 rpm
Air consumption	7.1 l/s
Inner hose diameter	10 mm
Sound-pressure level	95 dB
Weight	1.7 kg
Gross Weight	2.020 kg
Product Group	7AE



EAN

8717981362936