

BN 84229

Hexalobular (6 Lobe) socket pan head screws

Steel case-hardened

zinc plated blue





ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the introduction section.



[3D Cadenas](#)

Article#	ø nominal	d ₁	d ₂ max.	k max.		A~	t min.	t max.	L
3137662	2,2	2,2	4	1,6	X6	1,75	0,63	0,77	6
3137663									8
3137664									10
3137665									12
3137666									14
3137667									16
3137668	2,5	2,5	5	2,1	X8	2,4	0,91	1,04	6
3137669									8
3137670									10
3137671									12
3137672									14
3137673									16
3137674	3	3	5,6	2,4	X10	2,8	1,01	1,27	8
3137675									10
3137676									12
3137679									14
3137680									16
3137682									20
3137684									25
3137686	3,5	3,5	7	2,6	X15	3,35	1,07	1,33	8
3137690									10
3137692									12
3137694									14
3137695									16
3137697									20
3137698									25

Article#	ø nominal	d ₁	d ₂ max.	k max.		A~	t min.	t max.	L
3137700	4	4	8	3,1	X20	3,95	1,27	1,66	8
3137702									10
3137706									12
3137707									14
3137709									16
3137710									20
3137711									25
3137712	5	5	9,5	3,7	X25	4,5	1,52	1,91	10
3137713									12
3137714									14
3137715									16
3137716									20
3137718									25