



Technical Datasheet **tasker® TSK1042 - 2x2x0,22 mm²** **Professional Flat Audio Cable**

rightly blue®

FirestoP®



A

CATEGORY

Flat Audio Cable (See Audio Catalogue)

- A:** Soft **Flame Retardant Night Blue PVC** Sheath.
Outer cable Dimension: 4,50x9,10 (±0,10) mm.
- B:** Shielding in O.F.C. red copper spiral covering 100%.
+ Tinned copper drain wire.
- C:** Cores Insulation with compact XLPE – Diam. Ø 1,10 mm (±0,10) mm.
Pairs Color: White/Red and White/Blue.
- D:** O.F.C. red copper - formation 28x0,10 mm.
Nom. Cross section 2x2x0,22 mm².

MARKING CUSTOM

tasker® TSK1042 2x2x0,22 mm² FLAT AUDIO PAIR CABLE – Made in Italy
This product is also available in **L.S.Z.H., PE, PUR**

Cable Properties

Conductor Resistance	90 Ω/Km ± 5%
Capacity Core/Core	75 pF/mt
Capacity Core/Shield	160 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C ±10%

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor Direct Burial	Esterno Interrato
			

INSTALLATION	X	Fixed	Fissa
Posa	X	Flexible Limited	Flessibilità limitata
	X	Dynamic (Drag Chain)	Mobile in Catena
		Dynamic (Torsion)	Mobile in Torsione

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. B / 06.06.2016
		