

CONNECTOR, FEMALE, 12-PIN, FOR KP8 PN, WIRE CROSS-SECTION UP TO 0.75 MM² AMOUNT: SEE TECHNICAL DATA



Product type designation	
Installation type/mounting	
Wall mounting/direct mounting possible	Yes; can be plugged into SIMATIC HMI device
Supply voltage	
Rated value (DC)	24 V; DC
Interfaces	
Number of pins HMI-side	12; Female
Number of pins device-side	12; Female, spring-loaded terminals
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	95 %
Mechanics/material	
Type of housing (front)	
• plastic	Yes

Dimensions

Width	16 mm
Height	20 mm
Thickness	20 mm

Scope of supply

Delivery unit in items	10; Without ejector
------------------------	---------------------

other

Note:	for KP8 PN
-------	------------

Usable in the following products

- Product 1 [6AV3688-3AY36-0AX0](#)

last modified: 12.03.2015