

## Product information

# 70 26 160

## Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900



⚡ 1000 V 

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft material
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- VDE-tested safety up to 1000 volts
- With elongated cutting edge
- With small bevel
- Vanadium electric steel, forged, multi stage oil-hardened

### General

|                 |  |
|-----------------|--|
| Article No.     | 70 26 160  |
| EAN             | 4003773018223                                    |
| Pliers          | chrome-plated                                    |
| Head            | chrome-plated                                    |
| Handles         | insulated with multi-component grips, VDE-tested |
| Weight          | 216 g  |
| Dimensions      | 160 x 55 x 20 mm                                 |
| Standard        | DIN ISO 5749 DIN EN 60900 IEC 60900              |
| REACH compliant | does not contain SVHC                            |
| RoHS compliant  | not applicable                                   |

### Technical details

|   |          |
|---|----------|
| Cutting capacities soft wire (diameter) | Ø 4.0 mm |
| VDE tested                              | yes      |

*technical change and errors excepted*