

Product information


97 21 215 B SB

- With threaded holes for cutting copper and brass screws threaded M 2.6 / M 3 / M 3.5 / M 4 and M 5
- Bolted joint for higher stability and even movement
- Special steel, high-strength

Crimping Pliers



General	
Article No.	97 21 215 B SB
EAN	4003773041283
Pliers	black lacquered
Handles	with multi-component grips
Weight	265 g
Dimensions	230 x 85 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
	
Application	non-insulated open plug-type connectors (plug width 6.3 mm)
Capacity in square millimetres	0.5 — 2.5 mm ²
Number of crimping positions	3
AWG	20 — 14


technical change and errors excepted




97 21 215 B



97 21 215 B



97 21 215 B



97 21 215 B