

Switching, Sensing and Control Solutions

from GENTECH INTERNATIONAL LTD


Grangestone Industrial Estate, Girvan, Ayrshire KA26 9PS, United Kingdom Telephone: +44 (0) | 1465-7|358|. Fax: +44 (0) | 1465-7|4974

Email: sales@gentech-international.co.uk Website: www.gentechinternational.com

PS1/PM1 & PS2/PM2 SERIES

POSITION SENSORS

The Gentech PSI and PS2 Series of magnetic reed switch position sensors provide reliability and a robust construction suitable for dirty, oily, greasy, wet and similarly harsh environments. Operated by a similarly packaged (PM Series) magnet, the combination is suitable for direct magnet or shunt operation. PS Series position sensors meet a wide variety of application needs in security and safety systems, office equipment, fluid level sensing and management, construction plant, the automotive and many other industries.



DESIGN FEATURES

- Normally open, normally closed or changeover contact options
- UL listed models, PS2/PM2 range, file no.E153493
- Robust potted assembly in glass filled Nylon 6.6 UL 94-HB housing
- Cost effective, easy to install. Termination leads can be left or right handed to suit individual requirements
- Proven reed switch reliability, contact ratings up to 100Vdc, 15watts

Operational Characteristics

	01	02	03
	SPST(NO)	SPST(NC)	SPDT
ts DC	500	130	130
lts AC	250	100	100
mps	1.0	0.3	0.3
Vatts	15	3	3
olts Ohms	800 0.15	200 0.2	200 0.2
	lts AC Imps Vatts	SPST(NO) Its DC 500 Its AC 250 Imps 1.0 Vatts 15 Volts 800	SPST(NO) SPST(NC) Its DC 500 130 Its AC 250 100 Imps 1.0 0.3 Vatts 15 3

The above contact ratings are for resistive loads. For inductive, capacitive and tungsten filament lamp loads refer to the circuit protection notebook.

TYPICAL APPLICATIONS

- Security switches
- Interlocked switches
- Pulse generation
- Position indicators
- Materials handling
- Hook switches

Environmental Specifications

Temperature Range	Operate and Storage	
Magnet and Sensor	-30° to +105°C	
Cable insulation	-30° to +70°C	

Electrical Connections


PS1 Range Switch Option 01 & 02 are fitted with 2 x 0.5 metre of 24AWG, 7/0.2mm stranded, with PVC insulation.

PSI Range Switch Option 03 is fitted with 3 x 0.5 metre of 24AWG, 7/0.2mm stranded, with PVC insulation.


PS2 Range Switch Option 01 & 02 are fitted with 2 x 0.5 metre of 20AWG stranded, UL1015 with orange PVC insulation.

PS2 Range Switch Option 03 is fitted with 3 x 0.5 metre of 24AWG stranded, ULI569 with black, yellow & blue PVC insulation.

PSI/PMI & PS2/PM2 (UL LISTING)



PMI02 MAGNET



Installation

Please contact Sales at Gentech for installation instructions (Ref. FI 1000-RI)

Applications

Please contact Sales at Gentech for applications relating to this product group.



Email: sales@gentech-international.co.uk Website: www.gentechinternational.com