

Beacon LED XL - High Output


BEACON XL 85CRI 3K MEDIUM BEAM L3 BLACK

2059714



Product features

- Integrated LED spotlight, black RAL 9005, compact and minimalist design, ideal for retail and display applications, die-cast aluminium body, passive cooling heatsink, beam angle: 34° medium beam, optics: Polycarbonate lens, colour temperature: 3000K warm white, total system power: 33W, total fixture output: 3744lm, luminaire efficacy: 113lm/W, LOR: 100%, colour rendering: Ra 85 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 800mA, electronic driver, non-dimmable, power factor: 0.9 electrical protection: CLASS II, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotation: 355°, vertical tilt: 90°, dimensions: Ø113x165x205mm, weight: 1.66kg.



PRODUCT OVERVIEW

Product name	BEACON XL 85CRI 3K MEDIUM BEAM L3 BLACK
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Museums & Galleries, Retail
ETIM Class	EC001744
E-number FI	4280874
E-number SE	7401255
Warranty	5 years
Fixture luminous flux (lm)	3744
Luminaire efficacy (lm/W)	113
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	85
Colour Consistency (SDCM)	3
Beam Angle (°)	34
Photobiological Risk Group	RG1
Total power consumption (W)	33
Product Voltage (V)	240
Electrical protection	Class II
Control gear type	Electronic ballast
Dimming method	N/A
Housing colour	Black
IP rating	IP20
IK rating	IK02
Product EAN number	5025768597147

Beacon LED XL - High Output

BEACON XL 85CRI 3K MEDIUM BEAM L3 BLACK
2059714

DATA TABLE

General data

Product name	BEACON XL 85CRI 3K MEDIUM BEAM L3 BLACK
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Museums & Galleries, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4280874
E-number SE	7401255
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3744
Luminaire efficacy (lm/W)	113
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	85
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	34
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	33
Mains voltage (V)	220-240V
Product Voltage (V)	240
Lamp power factor	0.9
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	N/A
Drive current (mA)	800
Inrush Current (A)	30
Inrush Duration (µs)	200
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	12
Max. Luminaires per 16A C Breaker	20
Max. Luminaires per 10A B Breaker	12
Max. Luminaires per 16A B Breaker	20

Beacon LED XL - High Output

BEACON XL 85CRI 3K MEDIUM BEAM L3 BLACK

2059714

Lifetime data

Lifespan L70 B50	72000
Lifespan L80 B20	72000
Lifespan L90 B10	33000


Physical data

Housing colour	Black
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	85
Nominal Product Width (mm)	165
Nominal Product Height (mm)	205
Nominal Product Diameter (mm)	113
Weight (kg)	1.365

Packaging

Single packaging type	Carton
Product EAN number	5025768597147
Packaging single length / height (cm)	25.0
Packaging single width (cm)	19.5
Packaging single depth (cm)	20.0
DUN14 (outer)	05025768597147
Units per outer package	1
Packaging outer length / height (cm)	25.0
Packaging outer width (cm)	19.5
Packaging outer depth (cm)	20.0

PHOTOMETRY



TECHNICAL DRAWINGS

