

Collet chuck shape E4 type ER

With collet chuck cylinder mount

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Other designs available on request
- When selecting ER collet chucks, shape B should be used where possible



Art. no.	22778 148
Brand	ORION
Manufacturer Part Number	22778148
VDI mount diameter	30 mm
Collet type	ER 25
Min./max. clamping range	2-16 mm
Projecting length	57 mm
Outer diameter	68 mm
Height	28 mm
Length	22 mm
Gross Weight	1.100 kg
Product Group	2AC

EAN

405362546536 1