

Push rod clamp

Small angular base



Application:

For quick and secure clamping on machine tables and appliances.

Execution:

- Compression and tension clamp with small angular base
- Individual parts galvanised
- Long push rod version
- Case-hardened and lubricated bearing bushes
- Ergonomic, oil-resistant handle with large hand rest and soft components.

Advantage:

- Handle can be adjusted at any angle to the base surface

Delivery:

With thrust bolt and protective cap



Art. no.	26217 030
Brand	AMF
Manufacturer Part Number	94136
Size	3
Min./max. hole distance	29.5-42.5 mm
Bore diameter	6.5 mm
Clamping stroke	32 mm
Retaining force	2500 N
Clamping height	25 mm
Width of angled base	13 mm
Length	140 mm
Height	108 mm
Thumbscrew size	M8 x 35 mm
Gross Weight	0.430 kg
Product Group	260

EAN

4020772094133