

## infinitely adjustable clamp, complete



### Application:

For clamping workpieces. It is designed to withstand extremely high loads and is particularly suitable for clamping cutting tools and punches.

### Version:

- made of steel, forged, tempered and galvanised.

### Advantage:

- The infinitely variable adjustable clamp quickly spans various clamping heights without any additional support and requires little space on the machine table.



<b>Art. no.</b>	<b>26223 040</b>
<b>For table grooves according to DIN 650</b>	18 mm
<b>Min./max. clamping height</b>	0-75 mm
<b>Clamping shoe length</b>	140 mm
<b>Clamping shoe width</b>	50 mm
<b>Bore diameter</b>	17 mm
<b>Distance 2</b>	60 mm
<b>Distance</b>	30 mm
<b>Distance 1</b>	55 mm
<b>Slot nut width of clamping screw</b>	18 mm

### EAN-Code

4020772074937