

## Flat-bed hand truck, 2-axle with towing eye

Open, carrying capacity 700 kg to 1250 kg

**fetra**  
Transportgeräte

### Execution:

- Modular system
- From welded profile steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Load area covered with slip-resistant phenolic resin coated waterproof plywood
- Wheels either with solid rubber or air tyres, hubs with roller bearings
- Automatic locking brake acting on the front wheels, according to EN 1757-3
- Drawbar eye, internal diameter 32 mm
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



<b>Art. no.</b>	<b>50267 863</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	6404LZ
<b>Length</b>	1545 mm
<b>Height</b>	1200 mm
<b>Loading surface length</b>	1200 mm
<b>Width</b>	800 mm
<b>Loading-surface width</b>	800 mm
<b>Loading surface size</b>	1200 x 800 mm
<b>Loading-surface height</b>	490 mm
<b>Load-carrying capacity</b>	1000 kg
<b>Total stop optional</b>	No
<b>Wheel width</b>	100 mm
<b>Wheel diameter</b>	400 mm
<b>Material of wheel</b>	Air
<b>Gross Weight</b>	68.000 kg
<b>Product Group</b>	5AE

### EAN

4017976214030