

## Parallel vice 80–150 mm, heavy-duty version

With rear opening action, made of grey cast iron



### Execution:

- High-quality grey cast iron with pearlitic texture
- Hardened, ribbed steel jaws can be swapped for smooth, ground steel jaws
- Smooth-running spindle with trapezoidal thread
- High-quality hammertone finish, green (similar to RAL 6011)

### Advantage:

- Excellent clamping precision thanks to long, prismatic precision guide
- Spindle protected from dirt and damage by covering



<b>Art. no.</b>	<b>51035 150</b>
<b>Jaws width</b>	125 mm
<b>Min./max. clamping width</b>	0-200 mm
<b>Clamp in depth</b>	75 mm
<b>Weight</b>	29 kg
<b>Colour</b>	Green
<b>Material</b>	Grey cast iron
<b>Product Group</b>	Prod. Gr. 512