

## METABO cordless hammer drill SB 18 LT

Li-ion 18 V

metabo®

### Application:

For drilling boreholes in particularly solid materials using mechanical impact.

### Version:

- Spindle with hexagon socket for screwdriver bits for working without a drill chuck
- Integrated LED work light
- Battery capacity display



<b>Art. no.</b>	<b>71037 323</b>
<b>Model</b>	SB 18 LT
<b>Battery included</b>	Yes
<b>Applications</b>	Light screw/drill application
<b>Manufacturer Article Number</b>	602103500
<b>Type of rechargeable battery/battery</b>	Li-Ion
<b>Number of rechargeable batteries/batteries</b>	2 PCS
<b>Rechargeable battery/battery capacity</b>	4 Ah
<b>Battery voltage</b>	18 V
<b>Max. drilling diameter in steel</b>	13 mm
<b>Idle speed 2nd gear min./max.</b>	0-1600 rpm
<b>Max. drilling diameter in wood</b>	38 mm
<b>Idle speed 1st/2nd gear min./max.</b>	0-450 / 0-1600 rpm
<b>Max. impact rate</b>	27200 rpm
<b>Weight</b>	1.9 kg
<b>Max. torque hard/soft</b>	60 / 34 Nm
<b>Max. torque for hard screwing application</b>	60 Nm
<b>Max. torque for soft screwing application</b>	34 Nm
<b>Max. torque</b>	60 Nm
<b>Min./max. drill chuck span width</b>	1.5-13 mm
<b>Included in delivery</b>	2x rechargeable batteries, ASC 30-36 V charger, quick-action drill chuck, belt hook and bit depot, in plastic case

### EAN-Code

4007430213587