

## Temperature USB Datalogger



**Records up to 32,000 readings**  
 Datalogs Temperature readings with a user programmable sample rate

### Features:

- Datalogs up to 32,000 temperature readings
- Selectable data sampling rate: 2s, 5s, 10s, 30s, 1m, 5m, 10m, 30m, 1hr, 2hr, 3hr, 6hr, 12hr, 24hr
- User-programmable alarm thresholds
- Status Indication via Red/Yellow LED and Green LED
- Long battery life (approx. 1 year)
- Complete with 3.6V Lithium battery, protective USB cap, mounting bracket, and Windows<sup>®</sup> 98, 2000, XP, Vista, 7, 8 and 10 compatible analysis software



Monitors Temperature level in a warehouse or storage room.

Specifications	Range	Resolution	Accuracy (%rdg+digits)
Temperature	-40 to 158°F	0.1°F/°C	±1.8°F (14 to 104°F)
	-40 to 70°C		±3.6°F (all other ranges) ±1.0°C (-10 to 40°C) ±2.0°C (all other ranges)
Datalogging interval	2 seconds to 24 hours		
Memory	32,000 points		
Dimensions	5.1 x 1.1 x 0.9" (130 x 30 x 25mm)		
Weight	1oz (20g)		

### Ordering Information:

TH10 .....Temperature USB Datalogger  
 42299 .....3.6V Lithium Batery (pkg of 2)

