






Artikel-Nr.: 742164

Bez.: UHF-Kupplung, Lötausführung, Teflon-Isolation, Aircell 7



Impedance	Non-constant
Frequency range	0-300 MHz
Voltage rating	500 volts peak
Temperature range	-65°C to 155°C
Mating	5/8-24 UNEF thread coupling
Cable affixment	Braid solder, solderless clamp, set screw clamp and crimp

6	Braid Clamp	Brass	Silver
5	Gasket	Rubber	Red
4	Insulator	Teflon	White
3	Nut	Brass	Nickel
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish



NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER JIS-C3604
2. TEFLON MIL-P-19458
3. CONNECTOR INTERFACE PER MIL-STD-248A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 μ" THICK OVER COPPER STRIKE
6. GOLD PL 1-3μ" OVER NICKEL PL 70 μ" THICK OVER COPPER STRIKE

www.bkl-electronic.de

Technische Änderungen vorbehalten. Ausführungen können variieren. Sollten Sie ein Muster benötigen kontaktieren Sie uns bitte.

BKL-ELECTRONIC Kreimendahl GmbH • Märkenstück 14 • 58509 Lüdenscheid

Tel: +49 (0)2351-3621-0 • Fax: +49 (0)2351-3621-29 • info@bkl-electronic.de

