


AC2413



AS-Interface CompactLine module

CompactModule 4 SB



Electrical data	
Operating voltage	[V] 26.5...31.6 DC; ("supply class 2" to cULus)
Max. current load total	[A] 4
Operating conditions	
Ambient temperature	[°C] -25...80
Protection	IP 67; ("enclosure type 1" according to cULus; when flat cables are used E7400x / E7401x)
Tests / approvals	
EMC	EN 50295
Mechanical data	
Weight	[g] 272.5
Type of mounting	AS-i flat cables directly connectable
Materials	PA 6.6; socket: brass nickel-plated; threaded inserts in the lower part: brass nickel-plated; O-ring: FKM; piercing contacts: CuSn6 nickel-plated and tin-plated
Accessories	
Accessories (optional)	Stainless steel sleeve, for installation in case of high mechanical stress , E70402

AC2413



AS-Interface CompactLine module

CompactModule 4 SB

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

- 1 AS-i +
- 2 external voltage -
- 3 AS-i -
- 4 external voltage +
- 5 protective earth (FE)

Connector: M12

