

stay connected

MSUD VALVE PLUG FORM A 18MM

PUR 3X0.75 YELLOW, UL/CSA, drag ch 3m


Form A (18 mm) 24 V AC/DC with LED


Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration










stay connected



Product may differ from Image

Approvals





| 18001 |
|-------|
|-------|

| Technical Data | | |
|-------------------------------|--|--|
| Operating voltage | 24 V AC/DC ±25 % | |
| Operating current per contact | max. 4 A | |
| Locking of ports | M3 (recommended torque 0.4 Nm) | |
| Protection | IP67 inserted and tightened (EN 60529) | |
| Housing | Black plastic (gray on request) | |
| Cables | | |
| Cable number | 036 | |
| No./diameter of wires | $3 \times 0.75 \text{ mm}^2$ | |
| Wire isolation | PP (bk, num, gnye) | |
| C-track properties | 5 Mio. | |
| Torsion | 2 Mio. ± 180°/m | |
| Jacket Color | yellow | |
| Shore hardness outer jacket | 90 ± 5A | |
| Material (jacket) | PUR (UL/CSA) | |
| Outer diameter | approx. 5.9 mm | |
| Bend radius (fixed) | 5 × outer Ø | |
| Bend radius (moving) | 10 × outer Ø | |
| Temperature range (fixed) | -40+80 °C | |
| Temperature range (mobile) | -25+80 °C | |
| General data | | |
| Temperature range | -25+85 °C, depending on cable quality | |
| Commercial data | | |

INTERNET DATA SHEET for Article Number 7000-18001-0360300



stay connected

| country of origin | CZ |
|------------------------|----------|
| customs tariff number | 85444290 |
| minimum order quantity | 1 |