

Power supply, external, for Mobile Panel IWLAN SW incl. one PS cable for Switzerland additional information, amount and content: see technical data

General information

Product type designation External power supply unit

Control elements

Connection type

• Cable length 3 m

Supply voltage

Type of supply voltage 100 - 240 V AC

Rated value (DC) 12 V; Output side

Input current

Current consumption (rated value) 1.4 A; 50 - 60 Hz

Output current

per output 5 A

Power

Emitted active power 60 W; max.

Interfaces

HMI-side interface Connector 5.5 mm jack (-) / 2.1 mm pin (+) 12 V DC

EMC

Emission of radio interference acc. to EN 55 011

• Limit class A, for use in industrial areas Yes; EN61000-4-2,3,4,5,6,8,11 light industry level

Standards, approvals, certificates

CE mark Yes; UL69950, TÜVEN600950-1, BSMI CNS14336, CCC GB4942 approved

CCC Yes

Ambient conditions

Ambient temperature during operation

• min. -10 °C
• max. 50 °C

Ambient temperature during storage/transportation

• min. -20 °C
• max. 85 °C

Relative humidity

• Operation, max. 90 %

Cables

Cable length 0.9 m
Color of cable sheath Black

Mechanics/material

Material
• Plastic Yes
Enclosure color (front) Black
Enclosure color (rear) Black

Dimensions

Width 125 mm
Height 50 mm
Thickness 31.5 mm

Weights

Weight without packaging 525 g
Weight incl. packaging 710 g

Scope of supply

Delivery quantity in pieces 1; Incl. AC and DC connecting cable
• Parts per unit 1; AC cable for CH

Other

Merchandise Yes
Manufacturer name SIEMENS AG
Manufacturer's address Gleiwitzerstraße 555, 90475 Nuremberg, Germany
Target devices for Mobile Panel IWLAN

Usable in the following products

• Product 1 [6AV6645-0DD01-0AX0](#)
• Product 2 [6AV6645-0DE01-0AX0](#)
• Product 3 [6AV6645-0DB01-0AX0](#)
• Product 4 [6AV6645-0DC01-0AX0](#)
• Product 5 [6AV6645-0DD01-0AX1](#)
• Product 6 [6AV6645-0DE01-0AX1](#)
• Product 7 [6AV6645-0EB01-0AX1](#)
• Product 8 [6AV6645-0EC01-0AX1](#)

last modified: 10/13/2017