

ACS480-04-05A7-4



ACS480-04-05A7-4 Pcont.max:2,2kW, Icont.max:5,3A

General Information

Global Commercial Alias	ACS480-04-05A7-4
Product ID	3AXD50000047768
ABB Type Designation	ACS480-04-05A7-4
EAN	6438177458968
Catalog Description	ACS480-04-05A7-4 Pcont.max:2,2kW, Icont.max:5,3A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
EAN	6438177458968
Invoice Description	ACS480-04-05A7-4 Pcont.max:2,2kW, Icont.max:5,3A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	FIPSEEXPU US Drive Services SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU FIDRIEXPU

Technical

Frequency (f)	50/60 Hz
Input Voltage (U_{in})	380 ... 480 V
Number of Phases	3
Output Current, Normal Use	5.6 A
Output Power, Light-Overload Use	2.2 kW
Output Power, Normal Use	2.2 kW

Additional Information

Product Main Type	ACS480-04-05A7-4
-------------------	------------------

Product Name

Frequency Converter

Categories

Drives → Low voltage AC drives → General purpose drives

