

PRODUCT-DETAILS

XQMS0505

KFF STR S/STEEL CONNECTORS 25MMX25M



General Information

Extended Product Type	XQMS0505
Product ID	7TCA297070R0111
EAN	5011949217591
Catalog Description	KFF STR S/STEEL CONNECTORS 25MMX25M
Long Description	Liquid Tight Fitting for Covered Conduit, Straight with External Male Thread, Conduit Size 25mm, M25 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Stainless Steel AISI 316L, Nylon Seals

Ordering

EAN	5011949217591
Customs Tariff Number	7307221000

Dimensions

Product Net Weight	.24 lb 108.844 g
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	For Insertion Into Threaded Entries & Knockouts Using a Locknut to Secure
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Stainless Steel with Nylon Seals
Number of Batteries	0
Product Name	stainless steel fitting for conduit
Product Type	Straight Fitting with External Thread for Covered Conduit
Size	Conduit Size 25mm ; M25 Thread
Special Functions	Very High UV Protection and Mechanical Protection
Standards	UL E60625, BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210253893

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	XQMS0505
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	XQMS0505

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

