4-2337815-5 ACTIVE

Mini-SAS HD

TE Internal #: 4-2337815-5


Mini-SAS HD Cable Assembly, 16 Positions, 13.12 ft [4 m], 12 Gb/s, Shielded, 26 AWG, .128 mm², Round Jacketed Twinax, Mini-SAS

HD Plug

View on TE.com >



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Cable Assembly Type: Mini-SAS HD

Wire Size: .128 mm²

Shielded: Yes

Cable Assembly Length: 4 m [13.12 ft]

Features

Product Type Features

Cable Assembly Category	High Speed
Cable Assembly Type	Mini-SAS HD
Connector Type (End A)	Mini-SAS HD Plug
Connector Type (End B)	Mini-SAS HD Plug
Cable Style	Round Jacketed Twinax
Configuration Features	
Number of Positions	16
Number of Pairs	8
Number of Signal Positions	16
Electrical Characteristics	
Impedance	100 Ω
Signal Characteristics	

12 Gb/s

Data Rate



Cable Flammability Rating	CL2
Dimensions	
Wire Size	.128 mm²
Operation/Application	
Shielded	Yes
Halogen Free	No
Other	
Cable Assembly Length	4 m[13.12 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





TE Part # CAT-MHD6907-C117 Mini-SAS HD Cages



TE Part # 2214869-1 MiniSAS HD, 1x2 Rec Assy w/ weld



TE Part # 2214870-1 MiniSAS HD 1x4 Rec Assy w/ weld

Also in the Series | Mini-SAS HD



Mini-SAS Cages(11)



Pluggable I/O Cable Assemblies(18)



SAS & MiniSAS(10)



SATA & Micro SATA(1)

Customers Also Bought



TE Part #1658645-1 KIT,HDP-20,OVRMLD,PLUG,SIZE 1,



TE Part #1658648-1 KIT,HDP-20,OVRMLD,PLUG,SIZE 3,



TE Part #1658649-1 KIT, HDP-20, OVRMLD, RCPT, SIZE 3,



TE Part #1658650-1 KIT,HDP-20,OVRMLD,PLUG,SIZE 4,



TE Part #5750913-7 68 50SR CABLE CONN KIT



TE Part #YDTS26F15-05SNV001 PLUG ASSY



TE Part #5745173-2 CABLE CLAMP KIT,SZ 3

TE Part #EG8799-000 400R0111-22-9



TE Part #CM8837-000 MINIRAY-GUN-CASE



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2337815-5_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2337815-5_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2337815-5_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Product Specification

English

Product Specification

English