

30°, 45°, 60° chamfer cutters for milling inserts TCMT 1102.., TCMT 16T3..


ATORN®

Application

Universal use for chamfering and deburring.

Version

- with straight shank in accordance with DIN 1835 B
- Shaft tolerance h6
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm, M4 = 5.2 Nm



| | |
|---------------------------------------|------------------|
| Art. No. | 16107 321 |
| Chamfer angle | 45 Degree |
| Max. cutting edge diameter | 21 mm |
| Min. cutting edge diameter | 6.2 mm |
| Clearance length | 35 mm |
| Length | 90 mm |
| Shaft diameter | 20 mm |
| Number of cutting edges | 2 PCS |
| Suitable indexable insert no. | 1 |
| Suitable for indexable inserts | TC.. 1102.. |

EAN-Code

4050293111682