

SRGC clamping holder, positive, right

For copy, longitudinal face lathing with RC indexable insert

ATORN[®]

Application

For longitudinal turning with RC indexable insert

Version

- Precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17850 506
ISO name	SRGC R/L 2525 M06
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	18.8 mm
Programming size	32 mm
Suitable for indexable inserts	RC.. 0602..
Tool design	Right

EAN-Code

4050293563030