

Clamping heads, round version

ORION[®]

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating



Art. no.	22001 320
Brand	ORION
Manufacturer Part Number	22001320
Size	65
Design	With stem
Profile shape	Round with transverse grooves
Clamping diameter	8 mm
Length	58 mm
Min./max. clamping range diameter	8-10 mm
Gross Weight	2.000 kg
Product Group	2AO

EAN

4053625469260

