

META CLIP S3 slanted shelving system

Load capacity per bay 200 kg, galvanised



Execution:

- Basic rack, can be extended as required using an add-on rack
- FIFO principle (First In/First Out): The products stored first are used first (particularly important for goods with expiry dates)
- The uppermost level is fully available for loading since there are no crossbraces
- The shelves have an 18° incline so that goods stored on them virtually move themselves forward for removal
- The shelves have no protruding edges in the direction of the incline
- Low front stop side for easy removal of boxes and crates
- Shelves adjustable in increments of 25 mm
- Lateral guide available on request
- Planning dimensions basic shelf: Nominal length + 56 mm, frame depth 1228 mm (overall)



Art. no.	50164 802
Brand	META
Manufacturer Part Number	20091078
Height	2000 mm
Length	1356 mm
Depth	1228 mm
Nominal length	1300 mm
Nominal depth	1228 mm
Type of shelving	Shelving unit
Design	One side
Type of assembly	To insert
Surface	Zinc plated
ESD-capable	No
Grid dimension	25 mm
Number of shelves	4 PCS
Load-carrying capacity per shelf	200 kg
Load-carrying capacity per field	1200 kg
Number of frame	2 PCS
Made in	Germany
Gross Weight	99.425 kg
Product Group	508

EAN

4026212238198