

## Drill BE 10

450 watts, 1-speed, in box

**metabo**<sup>®</sup>

### Delivery

in cardboard box

<b>Art. no.</b>	<b>70005 004</b>
<b>Model</b>	BE 10
<b>Manufacturer Article Number</b>	600133810
<b>Nominal voltage</b>	230 V
<b>Max. drilling diameter in steel</b>	10 mm
<b>Max. drilling diameter in wood</b>	20 mm
<b>Power input</b>	450 W
<b>Power output</b>	240 W
<b>Idle speed 1st gear min./max.</b>	0-2400 rpm
<b>Cable length</b>	4 m
<b>Max. torque</b>	10 Nm
<b>Min./max. drill chuck span width</b>	1.0-10 mm
<b>Drill chuck type</b>	Quick action chuck
<b>Weight</b>	1.3 kg
<b>With rubber-coated handle</b>	No
<b>With overload protection</b>	No
<b>With restart protection</b>	No
<b>With right/left-hand rotation</b>	Yes
<b>With electronic feedback</b>	No
<b>With impulse function</b>	No



### EAN-Code

4007430203397