





Bits

1220-1223 1231-1234 Bit-Schraubendrehereinsätze

- DIN 3128
- für Kreuzschlitzschrauben






Code	Nr.	PH Gr.		"	L mm		
08010000	1220	0	C 6,3	1/4	25	5	10
08010001	1221	1	C 6,3	1/4	25	5	10
08010002	1222	2	C 6,3	1/4	25	5	10
08010003	1223	3	C 6,3	1/4	25	5	10
08030001	1231	1	C 8	5/16	32	9	10
08030002	1232	2	C 8	5/16	32	10	10
08030003	1233	3	C 8	5/16	32	10	10
08030004	1234	4	C 8	5/16	32	12	10


Außen  DIN 3126/ISO 1173
Phillips-Recess® DIN 5260
extra hart für Gewindeschrauben, Blechschrauben und andere gehärtete Schrauben

PZ1221-1223 Bit-Schraubendrehereinsätze

- für Kreuzschlitzschrauben (POZIDRIV/SUPADRIV®)
- extra hart






Code	Nr.	PZ Gr.		"	L mm		
08050001	PZ1221	1	C 6,3	1/4	25	5	10
08050002	PZ1222	2	C 6,3	1/4	25	5	10
08050003	PZ1223	3	C 6,3	1/4	25	5	10


Außen  DIN 3126/ISO 1173

1160-1169 Bit-Schraubendrehereinsätze

- DIN 3127/ISO 2351
- für Schlitzschrauben






Code	Nr.	a x b mm		"	L mm		
08070120	1160	0,5 x 3,0	C 6,3	1/4	25	4	10
08070121	1161	0,5 x 4,0	C 6,3	1/4	25	4	10
08070122	1162	0,6 x 3,5	C 6,3	1/4	25	4	10
08070123	1163	0,6 x 4,5	C 6,3	1/4	25	4	10
08070124	1164	0,8 x 4,0	C 6,3	1/4	25	4	10
08070125	1165	0,8 x 5,5	C 6,3	1/4	25	6	10
08070126	1166	1,0 x 5,5	C 6,3	1/4	25	4	10
08070130	1166/1	1,2 x 6,5	C 6,3	1/4	25	6	10
08070127	1167	1,2 x 8,0	C 6,3	1/4	25	6	5
08070128	1168	1,6 x 8,0	C 6,3	1/4	25	6	10
08070129	1169	1,6 x 10,0	C 6,3	1/4	25	14	10


Außen  DIN 3126/ISO 1173

1350-1360 Bit-Schraubendrehereinsätze

- für Innenvielzahnschrauben (XZN®)






Code	Nr.	Gr.		"	L mm		
08200004	1350	M4	C 6,3	1/4	25	4	10
08200010	1356	M5	C 6,3	1/4	25	5	10
08200011	1357	M6	C 6,3	1/4	25	5	10
08200012	1358	M8	C 8	5/16	28	10	10
08200013	1359	M10	C 8	5/16	38	15	10
08200014	1360	M12	C 8	5/16	38	20	10


Außen  DIN 3126/ISO 1173
DIN 65254 (M4, M5, M6)

1410-1421 1430-1435 Bit-Schraubendrehereinsätze

- für Innen TORX®-Schrauben



Code	Nr.	Gr.		mm	"	L mm		
08130006	1410	T 6	C 6,3	1/4	25	5	10	
08130007	1411	T 7	C 6,3	1/4	25	5	10	
08130008	1412	T 8	C 6,3	1/4	25	5	10	
08130009	1413	T 9	C 6,3	1/4	25	5	10	
08130010	1414	T 10	C 6,3	1/4	25	5	10	
08130015	1415	T 15	C 6,3	1/4	25	5	10	
08130020	1416	T 20	C 6,3	1/4	25	5	10	
08130025	1417	T 25	C 6,3	1/4	25	6	10	
08130027	1418	T 27	C 6,3	1/4	25	6	10	
08130030	1419	T 30	C 6,3	1/4	25	6	10	
08130040	1420	T 40	C 6,3	1/4	25	7	10	
08130045	1421	T 45	C 6,3	1/4	25	8	10	
08140027	1430	T 27	C 8	5/16	35	11	10	
08140030	1431	T 30	C 8	5/16	35	11	10	
08140040	1432	T 40	C 8	5/16	35	12	10	
08140045	1433	T 45	C 8	5/16	35	14	10	
08140050	1434	T 50	C 8	5/16	35	15	10	
08140055	1435	T 55	C 8	5/16	35	20	10	

Außen  DIN 3126/ISO 1173

Verwendungszweck:

Nr. 1416, Gr. T20, für die Türgriffverschraubung an Mercedes Benz Typ 168 und Typ 203




Nr. 1421, Gr. T45, zum Ein- und Ausbau der vorderen Türen am VW Golf III und Vento ab Bj. 93


Nr. 1435, Gr. T55, zum Betätigen der Schrauben an der Rücksitzbank am BMW X6 Modell E71, 7er Serie Modell F01/F02

1440-1446 Bit-Schraubendrehereinsätze

- mit Bohrung in der Antriebsspitze
- für Innen TORX®-Schrauben (TORX® TAMPER RESISTANT)






Code	Nr.	Gr.		mm	"	L mm		
08160010	1440	T 10	C 6,3	1/4	26	6	10	
08160015	1441	T 15	C 6,3	1/4	26	6	10	
08160020	1442	T 20	C 6,3	1/4	26	6	10	
08160025	1443	T 25	C 6,3	1/4	26	6	10	
08160027	1444	T 27	C 6,3	1/4	26	6	10	
08160030	1445	T 30	C 6,3	1/4	26	6	10	
08160040	1446	T 40	C 6,3	1/4	26	7	10	

Außen  DIN 3126/ISO 1173


1427 Bit-Schraubendrehereinsatz

- für Innen TORX®-Schrauben



Code	Gr.		"	L mm		
08131025	T 25	C 6,3	1/4	65	18	1

für 3er und 5er BMW

Außen  DIN 3126/ISO 1173