



► (RTSKP5) Bayonet Type with Cable Lug
RT-K02 (1000) SKP5



Max. operating temperature : -50 °C / +400 °C
Standard cable types : Fiber glass + fiber glass + braided wire
Sensor type : DIN/EN60751 Class "B" 1xPT-1000

► Technical drawing



Diameter (M) : 9,4 mm
Immersion Length (L) : 26 mm
Cable Length (K) : 2 meter