


EBC010



Splitter box

ZDO8H059MSS0000-00STAK120MSS




Application	
Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes
Electrical data	
Operating voltage [V]	10...30 DC; ("supply class 2" to cULus)
Max. current load per module/slot [A]	4
Max. current load total [A]	12
Outputs	
Electrical design	PNP

EBC010



Splitter box

ZDO8H059MSS0000-00STAK120MSS


Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67; ("enclosure type 1" according to cULus)
Mechanical data		
Weight	[g]	304.5
Dimensions	[mm]	33 x 60 x 152
Materials		PA
Number of ports splitter box		8
Connector type		M12
Displays / operating elements		
Display	switching status	8 x LED, yellow
	operation	1 x LED, green
Accessories		
Accessories (supplied)		Protective caps: 2 labels: 8
Remarks		
Pack quantity		1 pcs.
Electrical connection - Connection		
Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm		
		



Splitter box

ZDO8H059MSS0000-00STAK120MSS

Connection



Electrical connection - slot

Connector: 8 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

