


CHINA SOCKET MODULE

China (white)
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 250 V AC
-------------------	---------------

Operating current	max. 10 A
-------------------	-----------

General data

Mounting method	DIN-rail mountable (EN 60715)
-----------------	-------------------------------

Connection	Screw terminals: max. 2 × 4 mm ²
------------	---

Dimensions H × W × D	68×47×57 mm
----------------------	-------------

Commercial data

country of origin	FR
-------------------	----

customs tariff number	85366990
-----------------------	----------

minimum order quantity	1
------------------------	---