




MASI20 INSTALLATION TECHNOLOGY

Distributor AS-I and extern power, 3 potentials

5 ports, universal
3 potentials
without plug terminals

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 36 V DC
Current per connection	max. 8 A
Total current	max. 12 A
Isolation voltage	AS-Interface/Power 200 V, Power/Power 50 V (EN 60664-1)

General data

Protection	IP20
Connection	Screw terminal: single wire (0.2...2.5 mm ²), stranded wire (0.2...1.5 mm ²)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-20...+70 °C
Dimensions H × W × D	43×25×142 mm

Commercial data

country of origin	CZ
customs tariff number	85366990
minimum order quantity	1