

POTENTIAL TERMINAL BLOCK BL.YELL.BR.BL

Potential terminal block
blue/yellow/brown/blue

[Link to Product](#)


Illustration



	00	01	02	03	04	05	06	07	08	09
X0	—									—
X1										—
X2										—
X3										—

Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

General data

Protection	IP20
Dimensions H x W x D	70x56x32.5 mm
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)

Temperature range 0...+55 °C (storage temperature -40...+85 °C)

Commercial data

country of origin DE

customs tariff number 85369010

minimum order quantity 1