

WIRE CONNECTOR WITH CONTROL WIRE TAP 3 PCS.  
ACCESSORY FOR: 3VA6 400/600



### Model

|                     |             |
|---------------------|-------------|
| Product brand name  | SETRON      |
| Product designation | accessories |

### Connections according IEC

|  |                     |
|--|---------------------|
| Connectable conductor cross-section  |                     |
| <ul style="list-style-type: none"> <li>• for copper cable / finely stranded / minimum</li> </ul> | 50 mm <sup>2</sup>  |
| <ul style="list-style-type: none"> <li>• for copper cable / finely stranded / maximum</li> </ul> | 240 mm <sup>2</sup> |
| <ul style="list-style-type: none"> <li>• for copper cable / stranded / minimum</li> </ul>        | 50 mm <sup>2</sup>  |
| <ul style="list-style-type: none"> <li>• for copper cable / stranded / maximum</li> </ul>        | 300 mm <sup>2</sup> |
| <ul style="list-style-type: none"> <li>• for aluminum cable / stranded / minimum</li> </ul>      | 50 mm <sup>2</sup>  |
| <ul style="list-style-type: none"> <li>• for aluminum cable / stranded / maximum</li> </ul>      | 300 mm <sup>2</sup> |
| Wire stripping length  | 28 mm               |
| Tightening torque / when using copper cables   |                     |
| <ul style="list-style-type: none"> <li>• stranded</li> </ul>                                     | 42                  |
| <ul style="list-style-type: none"> <li>• finely stranded</li> </ul>                              | 42                  |





### Connections according UL

|                                     |        |
|-------------------------------------|--------|
| Wire stripping length               | 1.1 in |
| Connectable conductor cross-section |        |

- for copper cable / stranded / minimum 1 AWG
- for copper cable / stranded / maximum 600 kcmil
- for copper cable / finely stranded / minimum 1 AWG
- for copper cable / finely stranded / maximum 600 kcmil
- for aluminum cable / stranded / minimum 1 AWG
- for aluminum cable / stranded / maximum 600 kcmil

|  |           |
|--|-----------|
| Tightening torque / when using copper cables |           |
| • stranded                                   | 370 lb-in |
| • finely stranded                            | 370 lb-in |

## Certificates

| General Product Approval  | EMC   | Declaration of Conformity  | other   |
|---|---|--|---|
| <br>UL |  | <br>RCM | <br>EG-Konf. |
|   |   |  | <a href="#">Miscellaneous</a>   |

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JG13>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JG13>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9373-0JG13](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JG13)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



**last modified:**

08/28/2017