

BUILT-IN LUMINAIRE, STEADY LIGHT INTEGR. LED,
AC/DC 24V, RED



Figure similar

General technical data:

Product designation		blinklight lamp
Type of voltage		AC/DC
<ul style="list-style-type: none"> • of the operating voltage 		
Operating voltage		
<ul style="list-style-type: none"> • 1 for DC Rated value 	V	24
<ul style="list-style-type: none"> • 1 with AC at 50 Hz Rated value 	V	24
<ul style="list-style-type: none"> • 1 with AC at 60 Hz Rated value 	V	24

Mechanical data:

Product component Light source		Yes
Mounting type		Bayonet
Outer diameter of the signal column element	mm	75

Lamp:

Design of the optical signal		continous light
Type of light source		LED

Ambient conditions:

Ambient temperature during operation	°C	-20 ... +50
Protection class IP		IP65
Depth	mm	31
Height	mm	66
Width	mm	75

Certificates/ approvals:



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=8WD53205AB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD53205AB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=8WD53205AB&lang=en



SIEMENS

last modified:

15.01.2015