

M12 female contact Pack D0.8mm AWG 26-22



Part number	21 01 100 9025
Specification	M12 female contact Pack D0.8mm AWG 26-22
HARTING eCatalogue	https://b2b.harting.com/21011009025

Identification

Category	Contacts
Series	M12
Type of contact	Crimp contact
Description of the contact	Turned

Version

Gender	Female
Performance level	1

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm ²
Conductor cross-section	AWG 22 ... AWG 26

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances	Lead
-----------------------	------

Commercial data

Packaging size	1
Net weight	0.2 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440204 Contact for industrial connectors