

## Profile Semi Deep Surface 20

Profile Semi Deep Surface 20 EF/T 2m anodised

0022598



### Product features

- A semi deep 2000mm length anodised aluminium lighting profile that can be combined with slide (0022618) or click (0022619) opal diffusers with a maximum LED strip width of 20mm. The profile enables the cables to be hidden away and thanks to the good heat transfer capabilities it is possible to use LED sources of higher power. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



## PRODUCT OVERVIEW

Product name	Profile Semi Deep Surface 20 EF/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278024
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288225982

## DATA TABLE

### General data

Product name	Profile Semi Deep Surface 20 EF/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278024
Warranty	3 years

### Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	23
Nominal Product Height (mm)	25.1
Weight (kg)	0.53

### Packaging

Single packaging type	Carton
Product EAN number	5410288225982
Packaging single length / height (cm)	200.0

## Profile Semi Deep Surface 20

*Profile Semi Deep Surface 20 EF/T 2m anodised*  
0022598

Packaging single width (cm)	2.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288225982
Units per outer package	35
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

### TECHNICAL DRAWINGS

