

DMX Controller

RGB Controller with DMX Input

3036924



Product features

- RGB Controller (with DMX input/output). Can be linked to DMX Control plate for full control or using built in sequencer enables stand alone operation. Change program, speed, brightness without need for a control plate. 8A max Load.



PRODUCT OVERVIEW

Product name	RGB Controller with DMX Input
Technology	Controls
Environment	Interior
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC000533
Max load (A)	8
Input	Buttons
Input protocol	DMX
Output protocol	PWM
Number of channels	512
Electrical protection	Class III
IP rating	IP20
Product EAN number	8711971369240

DATA TABLE

General data

Product name	RGB Controller with DMX Input
Configured without PC	Yes
Technology	Controls
Environment	Interior
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Residential & Consumer, Retail
Operating temperature range (°C)	-10°C...+40°C
ETIM Class	EC000533

Electrical data

Max load (A)	8
Input	Buttons
Input protocol	DMX
Output protocol	PWM
Number of channels	512
Mains voltage (V)	24V
Electrical protection	Class III

DMX Controller

RBG Controller with DMX Input
3036924

Physical data

IP rating	IP20
Nominal Product Length (mm)	100
Nominal Product Width (mm)	72
Nominal Product Height (mm)	25
Weight (kg)	0.214

Packaging

Single packaging type	Carton
Product EAN number	8711971369240
Packaging single length / height (cm)	12.5
Packaging single width (cm)	8.2
Packaging single depth (cm)	4.6
Units per outer package	1
Packaging outer length / height (cm)	12.5
Packaging outer width (cm)	8.2
Packaging outer depth (cm)	4.6

Safety data

Optimal operating condition (°C)	-10-40
Compatible dimmers	36926