

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form



Art. no.	26195 040
Type	standard
Nominal dimension of groove	12 mm
Slot nut width	11.7 mm
Thread dimension	M10
Length	18 mm
Height	14 mm
Slot nut height	7 mm
DIN	508

EAN-Code

4020772080037